

## FL300 Recirculating Coolers for installation below a lab bench

The compact FL models are suited for a wide variety of cooling tasks. Installation under a lab bench saves valuable space. 2 variants: Air-cooled (FL) and water-cooled (FLW).



### Your advantages

- Ergonomic design and easy operation
- Splash-proof keypad
- Large, bright LED display
- Reliable Microprocessor PID temperature control
- Powerful immersion pumps, suitable for continuous operation
- Permissible temperature in return line +80°C
- Easy filling and Drain tap easily accessible
- Low liquid level protection with optical and audible alarm signal
- Integrated stainless steel bath tanks
- Removable ventilation grid
- Front drain
- No side vents, instruments can be placed right next to other equipment
- RS232 interface for PC connection
- IP class according to IEC 60529: 21
- Alarm output, potential-free change-over contact (max. 30 VA)

### Technical data

<b>Available voltage versions</b>		<b>Bath</b>	
Order No.	9 660 003	Bath tank	Stainless steel
<b>Available voltage versions:</b>			
9 660 003.01	100V/50-60Hz (Nema N5-15 Plug)		
9 660 003.13	230V/60Hz (Schuko Plug - CEE 7/4 Plug Type F)		
9 660 003.02	115V/60Hz (Nema N5-15 Plug)		
9 660 003.03	230V/50Hz (Schuko Plug - CEE 7/4 Plug Type F)		
9 660 003.04	230V/50Hz (UK Plug Type BS1363A)		
9 660 003.05	230V/50Hz (CH Plug Type SEV 1011)		
<b>Cooling</b>		<b>Other</b>	
Cooling of compressor	1-stage Air	Sound pressure level dbA	55
		Classification	Classification I (NFL)
		IP Code	IP 21
		Pump type	Centrifugal Pump
<b>Electronics</b>		<b>Dimensions and volumes</b>	
Temperature control	PID1	Weight kg	35
Temperature display	LED	Barbed fittings inner diameter	8/12 mm
Temperature setting	Keypad	Dimensions cm (W × L × H)	25 x 50 x 60
		Filling volume l	3 ... 4.5
		Pump connections	M16x1 male
<b>Temperature values</b>			
Setting the resolution of the temperature display °C	0.1		
Return flow temperature max. °C	80		

Temperature display resolution °C 0.1

**Performance values**

100V/50-60Hz (Nema N5-15 Plug)

100V/50Hz						100V/60Hz					
Cooling capacity (Water Glycol)						Cooling capacity (Water Glycol)					
°C	20	10	0	-10	-20	°C	20	10	0	-10	-20
kW	0.3	0.25	0.2	0.15	0.1	kW	0.3	0.25	0.2	0.15	0.1
Refrigerant	R134a					Refrigerant	R134a				
Filling volume g	140					Filling volume g	140				
Global Warming Potential for R134a	1430					Global Warming Potential for R134a	1430				
Carbon dioxide equivalent t	0.2					Carbon dioxide equivalent t	0.2				
Pump capacity flow rate l/min	15					Pump capacity flow rate l/min	15				
Pump capacity flow pressure bar	0.35					Pump capacity flow pressure bar	0.35				

230V/60Hz (Schuko Plug - CEE 7/4 Plug Type F)

220V/60Hz					
Cooling capacity (Water Glycol)					
°C	20	10	0	-10	-20
kW	0.3	0.25	0.2	0.15	0.1
Refrigerant	R134a				
Filling volume g	160				
Global Warming Potential for R134a	1430				
Carbon dioxide equivalent t	0.229				
Pump capacity flow rate l/min	15				
Pump capacity flow pressure bar	0.35				

115V/60Hz (Nema N5-15 Plug)

115V/60Hz					
Cooling capacity (Water Glycol)					
°C	20	10	0	-10	-20
kW	0.3	0.25	0.2	0.15	0.1
Refrigerant	R134a				
Filling volume g	155				
Global Warming Potential for R134a	1430				
Carbon dioxide equivalent t	0.222				
Pump capacity flow rate l/min	15				
Pump capacity flow pressure bar	0.35				

230V/50Hz (Schuko Plug - CEE 7/4 Plug Type F)

230V/50Hz					
-----------	--	--	--	--	--

Cooling capacity (Water Glycol)

°C	20	10	0	-10	-20
kW	0.3	0.25	0.2	0.15	0.1

Refrigerant	R134a
Filling volume g	133
Global Warming Potential for R134a	1430
Carbon dioxide equivalent t	0.19
Pump capacity flow rate l/min	15
Pump capacity flow pressure bar	0.35

230V/50Hz (UK Plug Type BS1363A)

230V/50Hz

Cooling capacity (Water Glycol)

°C	20	10	0	-10	-20
kW	0.3	0.25	0.2	0.15	0.1

Refrigerant	R134a
Filling volume g	133
Global Warming Potential for R134a	1430
Carbon dioxide equivalent t	0.19
Pump capacity flow rate l/min	15
Pump capacity flow pressure bar	0.35

230V/50Hz (CH Plug Type SEV 1011)

230V/50Hz

Cooling capacity (Water Glycol)

°C	20	10	0	-10	-20
kW	0.3	0.25	0.2	0.15	0.1

Refrigerant	R134a
Filling volume g	133
Global Warming Potential for R134a	1430
Carbon dioxide equivalent t	0.19
Pump capacity flow rate l/min	15
Pump capacity flow pressure bar	0.35

Benefits



**Precise**  
 PID Temperature control with set control parameters, temperature stability  $\pm 0.02 \dots \pm 0.2$  °C



**JULABO. Quality.**  
 Highest standards of quality for a long product life.



**Green technology.**  
Development consistently applied environmentally friendly materials and technologies.



**Satisfied customers.**  
11 subsidiaries and more than 100 partners worldwide guarantee fast and qualified JULABO support.



**100% Checked.**  
100% testing. 100% quality. Each JULABO Circulator undergoes thorough quality testing before leaving the factory.



**Quick start.**  
Individual JULABO consultation and comprehensive manuals at your disposal.



**Services 24/7.**  
Around the clock availability. You can find suitable accessories, data sheets, manuals, case studies, and more at [www.julabo.com](http://www.julabo.com).