


Handmade for quality

**SAF**  
WÄRMETECHNIK

## **LabHEAT<sup>®</sup>** standard heating mantles **series KM-G**

for operating temperatures up to 450°C

- for flasks, round bottom
- flexible glass yarn heating element  
*an even heat transfer and a gentle treatment of the glassware*
- high quality design  
*made by hand work*
- thermally insulated and earthed  
*thermed insulation prevents heat losses to the outside*
- sizes from 500 ml with Ø 60 mm bottom hole  
*for application with our magnetic stirrer KM-MR3050*
- four standard mounting clips  
*with appropriate accessories a minimum of effort allows to ensure a tilt-proof set-up or to integrate within support wall*
- with residual current detection (RCD)









## Technical specification

## KM-G

Nominal voltage	230 V AC
Nominal power output	see ordering details
Heating zones	see ordering details
Safety class	I
Heating element temperature	max. 450°C
Power supply cable	1,5 m with schuko-plug (earthed), heating zone switch and RCD switch

## Heating-zone selection

Switch position	0	1	2	3
1 heating zone				
Power	0	1/1		
2 heating zones				
Power	0	1/4	1/2	1/1

## Ordering details

Volume ml/l	Flask** Ø mm	Power W	Heating zones	Dimensions Ø x H mm	Part.-No.
25	41	65	1	110 x 60	95000025
50	51	75	1	120 x 70	95000050
100	64	120	1	150 x 80	95000100
250	85	180	2	160 x 90	95000250
500	105	250	2	180 x 100	95000500
1	131	450	2	210 x 110	95001000
2	166	600	2	250 x 140	95002000
3	185	800	2	280 x 150	95003000
4	207	900	2*	290 x 160	95004000
5	223	1200	2*	310 x 160	95005000
6	236	1400	2*	330 x 170	95006000
10	279	2000	2*	390 x 200	95010000
20	345	2200	2*	480 x 270	95020000

\*even available with 4 heating zones \*\* Schott Duran®

We also manufacture special heating mantles with other specifications - available on request

## Accessories

Tripod	series KM-DF	for higher stability of the heating mantles
Support ring	series KM-TR	to integrate the heating mantles within support wall
Magnetic stirrer	type KM-MR3050	for stirring medium in the glassflask

We supply a full range of controllers and temperature regulators

**SAF Wärmetechnik GmbH**  
**Weinheimer Str. 2a**  
**D-69509 Mörlenbach**

**Tel. + 49 (0) 6209 797 96-0**  
**Fax + 49 (0) 6209 797 96-29**

**E-Mail: info@saf-gmbh.de**  
**Internet: www.saf-gmbh.de**