

## **CC-K25**



Refrigerated Heating Bath with air-cooled refrigerating unit. Consisting of isolated cooling bath made of stainless steel with immersion thermostat. Pump and wetted parts made from stainless steel or high-resistant plastics. With adjustable overtemperature protection according to DIN 12876.

## Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

## Technical data according to DIN 12876

Operating temperature range	-30200 °C	
Temperature stability at 70°C	0,02 K	
temperature set point / display	5,7" colour Touchscreen	and the second se
Absolute accuracy	setup for calibration	
Internal temperature sensor	Pt100	
Sensor external connection	Pt100	
Interface digital	Ethernet, USB (Host u.	
	Device), RS232	
Safety classification	Class III / FL	
Heating power	2 kW	
Cooling power		
at 20°C	0,4 kW	hubers
at 0°C	0,35 kW	9
at -10°C	0,27 kW	
at -20°C	0,16 kW	
at -30°C	0,065 kW	
Refrigeration machine	air-cooled, natural	
	refrigerant	
Refrigerant	R290	
Refrigerant quantity	0,072 kg	
Gas warning sensor	without	Order-No.: 2012.0002.01
Pressure / Suction pump		
max. delivery	27 l/min	
max. delivery pressure	0,7 bar	
max. delivery (suction)	22 l/min	
max. delivery pressure (suction)	0,4 bar	
Pump connenction (optional)	M16x1 male	
Bath volume	25	
Width bath opening WxD	290x329 mm	
Bath depth	200 mm	
Height of bath opening	450 mm	
Overall dimensions WxDxH **	350x555x615 mm	
Net weight	36 kg	
sound pressure level +/- 4 dB(A)	50 dB(A)	
Power supply requirement	230V 1~ 50/60Hz	
max. current refrigerated bath	2 A	
5		

## Technical data according to DIN 12876

from Serial-No.:	149319	1.2/17
max. ambient temperature	40 °C	
min. ambient temperature	5 °C	
Degree of Protection	IP20	
max. Fuse	16A	
min. Fuse	10A	
max. current immersion thermostat	10 A	

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Accessories and periphery: mini-USB cable #54949\*, Drain valve with cap #6839, pump adaptor #19607, Note: When using Huber pump adapter: Polyglycol is not permissible to be used as a heat transfer fluid, adjustable base #40681, bath cover front #19598, bath cover back #6024, bath cover one piece #19599, trolley #6334, stainless steel test tube racks Typ 1-4, data cable #9472\*, nozzle #33288, DS level regulator #9580

\* standard equipment

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid: Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2% Example -5% voltage and + 2% frequency -> not allowed! -5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

1. Single-phase devices (230V/115V) -> with cable and plug

2. Three-phase devices with current consumption less than 63A -> with cable, without plug

3. Three-phase devices with current consumption greater than 63A -> without cable, without plug

\*\* Please respect space requirements. See operating conditions at www.huber-online.com