huber

Unichiller 060Tw

Chiller with water-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications.

Pilot ONE

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range temperature set point / display Internal temperature sensor Sensor external connection Temperature stability at -10°C

Interface digital

Safety classification Cooling power at 15°C

at 15°C at 0°C at -10°C at -20°C

Refrigerant

Refrigeration machine

Circulation pump max. delivery max. delivery pressure Delivery at 0,35 bar Delivery at 0,5 bar Delivery at 1,0 bar Delivery at 1,5 bar Delivery at 2,0 bar Delivery at 3,0 bar Delivery at 4,0 bar Delivery at 5,0 bar Pump connection

Volume of expansion

Cooling water connection
Consumption at water 15°C, flow 15°C
Consumption at water 15°C, flow 0°C
Consumption at water 15°C, flow -10°C
Consumption at water 15°C, flow -20°C
min. cooling water differential pressure
max. cooling water pressure
min. filling capacity

-20...40 °C

5,7" colour Touchscreen

Pt100 Pt100 0,5 K

Ethernet, USB (Host u. Device), RS232 Class I / NFL

6 kW 5 kW 3,1 kW 1,7 kW

water-cooled, CFC- and

Water-Coole HCFC-free R449A C3 80 l/min 5,6 bar 79 l/min 76 l/min 71 l/min

66 l/min 61 l/min 49 l/min 35 l/min 16 l/min

G1 1/4 male G1/2 male 230 l/h 230 l/h 152 l/h 70 l/h 1 bar 6 bar 5.9 l • Unichiller

Order-No.: 3026.0106.01

7,5 |

Technical data according to DIN 12876

Overall dimensions WxDxH ** 500x552x1261 mm

Net weight 173 kg

Power supply (3 Phase) 400V 3~ 50Hz *

Degree of Protection IP20 min. ambient temperature 5 °C max. ambient temperature 40 °C

from Serial-No.: 1.0/19

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original. Accessories and periphery: mini-USB cable #54949*, Hose coupling for G1 1/4 male*, hose coupling cooling water for G1/2 male*, cover expansion tank*, connection tubes, braided hoses for cooling water, Com.G@te.

* standard equipment

Output data valid for: Room temperature 20°C, cooling water inlet 15°C and 1 bar differential pressure between cooling water inlet and outlet. This temperature control unit has been designed to operate with cooling water up to 20°C. As the cooling water temperature increases, drop in the cooling power should be expected, and also an increased cooling water flow rate possible. Materiels used in the cooling water circuit include; copper, Stainless steel 1.4401, MS, PA, PPE, PTFE and EPDM. Please use suitable cooling water.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single-phase devices (230V/115V) -> with cable and plug
- 2. Three-phase devices with current consumption less than 63A -> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A -> without cable, without plug
- ** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com