huber

CC-300BX

Bridge heating thermostat with telescopic arm (up to 884 mm). Housing and all moistened parts in stainless steel. With cooling coil for water-cooling (3/8"). Pressure- and suction pump made of high-resistant plastic. With adjustable overtemperature protection according to DIN 12876.

Pilot ONF:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range

with water cooling

with refrigerator

Temperature stability at 70°C

temperature set point / display

Absolute accuracy

actual for collibration

Absolute accuracy setup for calibration
Internal temperature sensor Pt100
Sensor external connection Pt100

Interface digital Ethernet, USB (Host u. Device), RS232
Safety classification Class III / FL
Heating power convertible 3,0kW oder 4,0kW

Pressure pump yes
max. delivery 25 l/min
max. delivery pressure 0,7 bar
Suction pump yes
max. delivery (suction) 18.5 l/min

max. delivery pressure (suction) 0,4 bar
Pump connection M16x1 male
Immersion depth 175 mm

max. permissible kin. viscosity 50 mm²/s
Overall dimensions WxDxH ** 345x190x392 mm

Net weight 13 kg max. current 14 A

max. current (3 Phase)

Power supply convertible 230V 1~ 50/60Hz* or 400V 3~N 50/60Hz

Fuse 16 A
Fuse (3 phase) 3x16 A
Degree of Protection IP20
min. ambient temperature 5 °C
max. ambient temperature 40 °C

CC SOOK Jahr

Order-No.: 2007.0002.01

from Serial-No.: 234500 1.2/17

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

11 A

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com

Technical data according to DIN 12876

Accessories and periphery: mini-USB cable #54949*, Adapter nom. dia. 12*, dummy plugs, sleeve nuts thread M16x1*, connection tube silicon*, connection tubes, various baths * standard equipment

Output data valid for: Room temperature 20°C

In accordance with EN60034-1 the following voltage and frequency tolerances are valid: Voltage + / - 10%, as long as the frequency tolerance does not run in the opposite direction.

Example: -10% voltage and +3% frequency -> not allowed!

-10% voltage and -3% frequency -> allowed.

Information to Electromagnetic compatibility: Classification (disturbance) to EN55011: Class A, Group 1

Alternative (factory set) power supply - please quote configuration at time of ordering.

Standard delivery conditions - Power cable configuration:

- 1. Single-phase devices (230V/115V) -> with cable and plug
- 2. Three-phase devices with current consumption less than 63A -> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A -> without cable, without plug
- ** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com